

# Wireless Rugged Remote



## Easy-to-Use

- The remote control operation mode enables control of 6000, SLM and ELM Series projectors.  
Even when the user menu on screen is switched off during the show, the off screen read out provides you with the necessary information. By connecting the Wireless Rugged Remote to an ELM or SLM lamp house, in the lamp read mode all the specific lamp parameters can be shown.
- Designed with all possible usage situations in mind, this rock solid working partner can also be mounted within a 19" equipment rack. A shoulder strap provides added convenience when climbing trusses.
- The handy carrying case contains the following items:
  - Rugged Remote
  - Charger
  - Supplementary mains plugs; UK/US/AUS
  - SUBD9 male/female adaptor
  - Lamp communication cable
  - Shoulder strap
  - Manual

**PRODUCT SPECIFICATIONS****WIRELESS RUGGED REMOTE**

<b>Display</b>	4 lines Liquid Cristal Display fully backlit
<b>Keypad</b>	27 keys fully backlit 5 programmable function keys
<b>Connections</b>	Radio frequency transceiver 2 way hardwired remote XLR port lamp module info port to facilitate spare lamp management RS 232/422 port switch RS 422T -RS 422NT -RS232
<b>Communication (baud)</b>	XLR fixed at 57600 bps RS 232/RS 422 (9600 bps, 19200 bps, 38400 bps, 57600 bps, 115200 bps)
<b>Communication range</b>	wireless up to 100m (330ft)
<b>Address</b>	any number between 0 and 255
<b>Power supply</b>	6x NiCd AA rechargeable batteries (included) or standard batteries 15-30 V DC adaptor 2 charging modes: via external charger or via XLR port of the projector power save mode = automatically switched off after 10 minutes of inactivity
<b>Temperature range</b>	-15 -70° c (5F -158F)
<b>Weight</b>	remote control: 1,3 kg (2,8 lbs) receiver: 0,3 kg (0,6 lbs)

Last updated: 08 Nov 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.