

G60-W10

10,000 lumens, WUXGA, DLP laser phosphor projector



- **Great image quality**
- **Optimal integration capabilities**
- **Guaranteed service and support**

The G60 series expands the single-chip offering with six quality projectors between 7 and 10K. It opens up the possibilities to a wider range of applications while still relying on the valued Barco service and support.

The laser light source ensures great image quality, on the one hand, but also lower maintenance compared to most lamp-based projectors on the market. Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer.

The projectors are available in black and white, allowing you to choose the perfect fit for your specific environment. Their uniform compact size, the compatibility with other Barco products and the wide lens shift range enlarge the projectors flexibility.

TECHNISCHE SPECIFICATIES**G60-W10**

Type projector	Single chip DLP laser phosphor projector
Resolutie	1,920 x 1,200 (WUXGA)
Helderheid	9,000 ANSI lumens 9,500 center lumens 10,200 ISO lumens
Contrastverhouding	1,200:1 sequential; 6,000:1 dynamic; Extreme black: 100,000:1
Helderheidsuniformiteit	85%
Beeldverhouding	16:10
Type lens	G-lenses -0.36:1 / 0.75-0.95:1 / 0.95-1.22:1 / 1.22-1.52:1 / 1.52-2.92:1 / 2.90-5.50:1
Optische lensverschuiving	Vertical up to 100%, depending on lens Horizontal up to 30%, depending on lens Motorized zoom and focus Motorized lens shift
Kleurcorrectie	Yes
CLU (constante lichtuitvoer)	Yes
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000hrs
Verzegelde DLPTM-kern	Yes
Oriëntatie	360° rotation, no restrictions
3D	Active stereoscopic 3D
Beeldverwerking	Warp & blend possible via external tool
Trapeziumcorrectie	Yes
Ingangen	2x HDMI 1.4 / DVI-D / HDBaseT / 3G-SDI / VGA (D-Sub 15 pin) / RJ 45 Ethernet / RS232 in
Invoerresoluties	Up to 1,920 x 1,200 @ 60Hz refresh rates: 24Hz to 120Hz for 720p (1280x720) and 24Hz to 60Hz for WUXGA (1920x1200)
Softwaretools	Projector Toolset
Controle	IR, RS232, RJ45, 3.5mm phone jack for wired remote
Netwerkverbinding	10/100 Ethernet, RJ45
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	935W nominal, 1080W maximum
BTU/uur	3,190 BTU/h nominal; 3,690 BTU/h maximum
Stroom in stand-by	less than 0.5W
Geluidsniveau (standaard bij 25°C/77°F)	36dB(A) -40dB(A) depending on the used mode
Bedrijfstemperatuur	5 -40 °C (sea level)
Opslagtemperatuur	-10 to 60 °C
Vochtigheid in bedrijf	10 -85% RH, non-condensing
Vochtigheid bij opslag	5 -90% RH, non-condensing
Afmetingen (B x L x H)	without feet: 484 x 529 x 195 mm / 19.06 x 20.83 x 7.68 in
Gewicht	without lens: 22.7 kg / 50.1 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Garantie	Limited 3 years parts and labor

Last updated: 16 Mar 2023Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.