

ClickShare CSE-200+

Draadloze samenwerkingsoplossing om creatief inhoud te delen, implementeerbaar in bedrijven



- Tot 2 gebruikers op het scherm
- Delen vanaf laptop, tablet of smartphone
- Vloeiend schakelen tussen bekabelde en draadloze bronnen
- Verbeterde beveiligingsfuncties
- Aantekening-, blackboard- en touch back-ondersteuning op een 4K-canvas
- Centraal management
- Geleverd met 2 Buttons

Creativiteit stimuleert bedrijven. Door creatieve vergaderingen, brainstormen en discussies mogelijk te maken, verbetert de samenwerking tussen de teams en de bedrijfsresultaten. Met de draadloze samenwerkingsoplossing ClickShare zorg je voor moeiteloze ideevorming en efficiënte samenwerking in je bedrijf.

Ontdek wat er nieuw is in de laatste ClickShare-update

Verrijkt delen

De CSE-200+ biedt interactieve samenwerkingservaringen voor middelgrote vergaderruimten. Tot 2 personen kunnen gelijktijdig inhoud delen. Gebruikers moeten gewoon een apparaat met USB – de ClickShare Button – aansluiten op hun pc of Mac en op de knop drukken om de inhoud vanaf hun laptop op het grote scherm van de vergaderruimte te tonen. Met de ClickShare-apps kunnen gebruikers ook inhoud van hun laptop, mobiele telefoon of tablet delen. Zorg dat de laatste firmware-versie geïnstalleerd is op je basisstation om de beste ervaring te krijgen met de bureaubladapp.

Stimuleer de creativiteit in je hele bedrijf

De CSE-200+ is ontworpen voor implementatie in bedrijven. Het biedt een HDMI-ingang voor oude apparatuur, eenvoudig schakelen tussen draadloze en bekabelde bronnen, verbeterde beveiligingsfuncties, volledige netwerkintegratie, een breed scala aan interactiviteitsfuncties – waaronder aantekeningen, blackboarding en touch-backondersteuning op een 4K-canvas en centraal management. Met de CSE-200+ kunnen maximaal 2 personen tegelijkertijd inhoud delen. Het stimuleert ook brainstormen en productiviteit in je bedrijf.

De CSE-200+ is gemaakt met ISO 27001-gecertificeerde stromen en processen.

Door ClickShare CSE-200+ toe te voegen aan je vaste vergaderruimte (zoals een Microsoft Teams- of Zoom-ruimte), verbeter je de interactiviteit, productiviteit en samenwerking in je Microsoft Teams- en Zoom-vergaderingen. Het brengt de focus van vergaderen terug naar echt samenwerken.

PRODUCT SPECIFICATIONS**CLICKSHARE CSE-200+**

General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.14/10.15 (Catalina) Android 9 & 10 (ClickShare app) iOS 11, 12 & 13 (ClickShare app)
Video outputs	1x HDMI 1.4b
Video inputs	1x HDMI 1.2
Output resolution	4K UHD (3840*2160) @ 30Hz
Input resolutions	1920x1080 @60Hz
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
AirPlay Support	iOS 11, 12 & 13 / macOS 10.14, 10.15
Google Cast Support	Android 9, 10
Miracast support	Miracast R2 support on Windows 10
Frame rate	Up to 30fps*
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available for Windows, requires ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/b/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (back); 2x USB Type A 2.0 (back); 1x USB Type A 2.0 (front) Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard
*Note	*In optimal WiFi conditions with minimal WiFi interference and as measured during our quality validation. Check Network Deployment Guide for more info on WiFi optimisation and ideal configuration depending on your network environment.

ClickShare Base Unit dimensions

Dimensions (HxWxD)	39mm x 200mm x 202mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 50W (max) Standby:
Weight	900 gr

Last updated: 07 May 2021Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.