

S3-4K Jr Gen 2

Compact and cost-effective Event Master processor



The updated S3-4K Jr Gen 2 configuration is ideally suited for applications that do not require the full capacity of the S3-4K Gen 2 or E2 Gen 2. It comes configured with one Gen 2 input cards, two output cards, a 4K60 MVR and two mixers on an up to 4Kx2K canvas in the same 3 RU form factor as its bigger S3-4K Gen 2 brother. S3-4K Jr Gen 2 can easily grow with your shows through upgrades. Simply purchase and install additional cards into your system. With all cards installed you can even upgrade the S3-4K Jr Gen 2 to a fully loaded S3-4K Gen 2 system at any time.

Powerful features, easy operation

- Pre-loaded with six I/O cards
- Interlinking of S3-4K chassis allows expansion of inputs, outputs or layers
- Manage all versions of the system with the cross-platform Event Master Toolset
- Serviceable in the field and ready for future signal interfaces via the modular Event Master cards
- Optional dual redundant power supply for maximum peace of mind
- Projection blend and Native Test Pattern support
- LED Custom format and Native Test Pattern support

TECHNISCHE SPECIFICATIES**S3-4K JR GEN 2**

Live-effectencanvas	-10 Megapixels PVW/PGM -20 Megapixels PGM only
----------------------------	---

Video-ingangen	6 FHD@60 inputs via 1 Tri-combo card <ul style="list-style-type: none">■ Mix and match between 6 x FHD@60 to 2x 4K@60 inputs■ 4x SD/HD/3G/6G/12G SDI connectors (Tri-Combo card)■ 1x HDMI 2.0 (600MHz max)■ 1x DisplayPort 1.2 (660MHz max)
-----------------------	--

Video-uitgangen	8x FHD@60 / 12x 4K@30 / 6x 4K@60 outputs via 2 output cards (HDMI 2.0 4 outputs ea) <ul style="list-style-type: none">■ Multiviewer 4x HDMI 2.0 for 4x FHD@60 or 1 x 4K60 (600MHz max)■ 4x HDMI 2.0 when used as standard output card
------------------------	--

Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
----------------	---

Programma-uitvoer	<ul style="list-style-type: none">■ Up to 4 program outputs with mixing background and pip/key, configurable as single screens or tiled/blended widescreens (preview and Multi-Viewer not available in all configurations)■ Configurable for up to 8 x 4K@30 / 4 x 4096x2400@60■ Independent edge blending/feathering control for all four sides
--------------------------	--

Aux-uitgangen met schaalverdeling	<ul style="list-style-type: none">■ Route and Scale any source to any Auxilliary output■ User definable for up to 8 x 4K@30 / 6 x 4096x2400@60■ All outputs can be defined as Aux destinations for a total of 8 Aux outputs■ Output color correction. (preview and Multi-Viewer not available in all configurations)■ Upscale any source to any Super AUX array of screens
--	--

Mixers	<ul style="list-style-type: none">■ Native resolution background mixer per program screen■ Independent layer transitions or full Preview/Program transition■ Flexible layer allocation – 2 mixable or 4 single scalable PIP/key layers assignable to any Program output screens.
---------------	--

Geheugenruimte voor foto's	Up to 100 HD or 25 UHD. Import file size dependent.
-----------------------------------	---

Laageffecten	<ul style="list-style-type: none">■ Borders (hard, soft, halo) and drop shadows■ Color effects■ Strobe, H&V flip■ Luma, chroma and Cut/Fill keys (not all modes support keying)■ PIP moves via Keyframes
---------------------	--

Multiviewer	<ul style="list-style-type: none">■ Flexible user-definable layouts■ Monitor all Inputs and Outputs, including Preview and Aux■ 4 x FHD@60 outputs or 1 x 4K60■ Dedicated hardware same as E2 Gen2 Event Master Processor■ Source On Pvw/Pgm Indication in MVR■ Source on PVW/PGM reflected in the operation view■ Source on PVW/PGM available via TSL3.1 on network
--------------------	--

Uitbreidbaarheid	Linking is available as an user upgradeable option via adding Link Card.
-------------------------	--

TECHNISCHE SPECIFICATIES**S3-4K JR GEN 2**

HDCP	HDCP Compliance determined by installed cards.
Controle	<ul style="list-style-type: none">■ Event Master screen management software for PC or MAC■ Event Master Controllers■ WebUI■ JSON and Telnet API available■ Ethernet RJ-45, 1000/100/10 Mbps autosense
Onderhoudsgemak	<ul style="list-style-type: none">■ Field-Serviceable I/O and processing cards (not hot-swappable)■ Hot swappable power supplies, Optional redundant.
Geluidsniveau	<ul style="list-style-type: none">■ Max 51.3 dB avg. Fans at 100%■ As low as 34 dB with low fanspeed■ Fan speed is software managed based on operating temperature■ Reference ISO 7779
Afmetingen	<ul style="list-style-type: none">■ Height: 13.26 cm / 5.22 inches - 3 RU Rackmount■ Width: 43.2 cm / 17 inches without chassis handles, 48.3 cm / 19 inches with chassis handles attached■ Depth: 54 cm / 21.33 inches overall
Gewicht	21 kg / 46 lbs
Vermogen	Input power: 100-240Vac, 50/60Hz, 8.8A (x2), 826 Watt Ships with single power supply. Optional Dual-redundant, hot-swappable power supplies; available as upgrade.
Garantie	3 years parts and labor
Omgevingstemperatuur	0-40 C (32-104 F)
Omgevingsvochtigheid	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)

Last updated: 13 Mar 2023

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.