

Lente fixa de ângulo largo EN15

1.25: 1 (SX+)/1.16: 1 (WUXGA)



Faixa de Foco: 1,5 - 15,0 m

Razão de alcance

- SX+ 1.25:1
- 1080 / WUXGA 1.16:1

ESPECIFICAÇÕES TÉCNICAS**LENTE FIXA DE ÂNGULO LARGO EN15**

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Zoom ratio	No zoom Motorized focus
Focal length	23.98 mm
Focus Range	Standard: 1.5m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.4 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.16:1■ SXGA+ 1.25:1■ 720p 1.37:1■ XGA 1.71:1
	Image size tolerance +/-5%

Gerada em: 21 Jan 2018

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte www.barco.com para as últimas informações.