

ClickShare CSE-200

Sistema de apresentação sem fio para salas de reunião de pequeno e médio porte



- **Conexão sem fio à tela central**
- **Até 2 usuários na tela**
- **Compartilhe do laptop, tablet ou smartphone**
- **Recursos de segurança aprimorados**
- **Gerenciamento central**
- **Entregue com 2 Buttons**

A criatividade é um dos principais ativos da sua organização. Com o ClickShare, você pode ter certeza que as ideias receberão a atenção que merecem. O sistema de apresentação sem fio permite que os usuários compartilhem o conteúdo do seu laptop ou dispositivo móvel na tela da apresentação. Sem cabos, sem instalação, sem espera para participar.

Conecte-se para se diferenciar

O CSE-200 oferece a experiência do ClickShare para salas de reunião de pequeno e médio porte. Qualquer pessoa - incluindo convidados - podem se conectar com um clique e compartilhar imediatamente, sem necessidade de treinamento. Os usuários simplesmente conectam um dispositivo alimentado por USB - o ClickShare Button - no seu computador ou Mac e clicam no botão para levar o conteúdo do laptop à tela grande da sala de reunião. Com o Aplicativo do ClickShare, os usuários também podem compartilhar conteúdos dos seus celulares ou tablets.

Promovendo a colaboração

O CSE-200 foi projetado para implementações empresariais e oferece recursos de segurança aprimorados, uma gama mais ampla de opções de conectividade - incluindo suporte de AirPlay e Google Cast para conteúdo não HDCP - e gerenciamento central. Permitindo que até 2 pessoas compartilhem conteúdo simultaneamente, o CSE-200 garante conectividade direta à tela central e encoraja a colaboração. Para conveniência do usuário, os recursos de segurança do CSE-200 podem ser definidos para um dos três níveis predefinidos, dependendo das políticas e necessidades da empresa. Por fim, a API do dispositivo facilita substancialmente a integração na rede da empresa.

ESPECIFICAÇÕES TÉCNICAS**CLICKSHARE CSE-200**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	205mm x 115mm x 45mm (excl. antennas) / 8.1" x 4.5" x 1.8" 205mm x 150mm x 135mm (incl. antennas) / 8.1" x 5.9" x 5.3"
Power supply	Standard 110/220 V AC plug or Power over Ethernet (PoE Plus)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
Weight	600g / 1.32lbs
General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.12/10.13 (High Sierra) Android v5 & v6 & v7 & v8 & 8.1 (ClickShare app) iOS 8, 9 & 10 & 11 (ClickShare app)
Video outputs	1x HDMI
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 11.3 / Mac OS 10.13 El Capitan or higher
Google Cast Support	Android 8.1 Oreo
Frame rate	Up to 30 fps
Output resolution	1920x1200
Noise Level	Fanless
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available (depending on your operating system). May require ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 2x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years

Gerada em: 18 May 2018

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte www.barco.com para as últimas informações.