

# RLM-W8

Projektor de 8.000 lúmens, WUXGA, DLP



- **Qualidade de cor DLP com 3 chips**
- **Combinação e distorção integrada**
- **BarcoLink para distribuição rápida do sinal**

## **Apresentando combinação e distorção integrada**

Com um contraste aprimorado, opções de empilhamento rápidas e criativas, e recursos integrados de distorção para superfícies curvas, o RLM-W8 da Barco é uma escolha versátil para locais de médio e grande porte. Além disso, ele tem tecnologia de mesclagem para criar imagens compostas contínuas em telas de qualquer tamanho. O RLM-W8 segue a tradição da linha RLM de projetores silenciosos e de baixo consumo de energia.

## **Rápida distribuição de sinal**

Nossa tecnologia proprietária BarcoLink garante uma distribuição rápida do sinal entre os processadores de imagem e os projetores da Barco. Com o BarcoLink, os sinais são distribuídos em um cabo coaxial BNC, que não é apenas mais durável, mas também permite que você reduza seus custos.

**ESPECIFICAÇÕES TÉCNICAS****RLM-W8**

|  |  |
|--|--|
| Projector type                                 | WUXGA 3-chip DLP digital projector   |
| Technology                                     | 0.67" DMD™ x3  |
| Resolution                                     | 1,920 x 1,200  |
| Brightness                                     | 8,000 center lumens / 7,300 ANSI lumens*   |
| Contrast ratio                                 | 2,200:1 (standard) / 3,000:1 (CE)  |
| Brightness uniformity                          | 95%  |
| Aspect ratio                                   | 16:10  |
| ScenergiX                                      | Horizontal and vertical edge blending  |
| Lens type                                      | RLDW   |
| Lenses   | (fix)0.77:1 ; 1.16:1 ; (zoom) 1.45-1.74 ; 1.74-2.17 ; 2.17-2.9 ; 2.9-4.34 ; 4.34-6.76  |
| Optical lens shift                             | Vertical: -100% to +100% / Horizontal: -35% to +35% on zoom lenses   |
| Color correction                               | P7   |
| Lamps  | 2x330W   |
| Lamp lifetime                                  | 1,500 hours (typical) / 2,000 hours (maximum)  |
| Transport with lamp                            | Yes  |
| Lamp house, quick replace                      | Yes, auto lamp select  |
| Lamp warranty (field replace/ factory replace) | 120 days, 500 hours  |
| Sealed DLP™ core                               | Standard   |
| Optical dowser                                 | standard   |
| Picture-in-picture                             | Up to two sources simultaneously   |
| Orientation                                    | table -ceiling   |
| WARP   | Preset and customized values (RS232)   |
| Integrated web server                          | Yes  |
| 3D   | Passive circular polarized (optional)  |
| Inputs   | 2 x HDMI (HDCP 1,3); 5-BNC (RGBHV, RGBS/RGBsB;YUV); VGA (RGBHV, RGBS/RGBsB; YUV); cinch (RGBs, YUV); Composite video; S-Video; HSDI/ 3G HDSDI /SDI/BarcoLink |
| Input resolutions                              | From NTSC up to UXGA (1600x1200), including WUXGA (1920x1200)  |
| Max. pixel clock                               | 165 MHz  |
| Software tools                                 | Projector Toolset, Android app   |
| Control  | Minijack + IR, RS232, 12v trigger  |
| Network connection                             | 10/100 base-T, RJ-45 connection  |
| Power requirements                             | 90-240V / 50-60Hz  |
| Max. power consumption                         | 850W / STBY  |
| Noise level (typical at 25°C/77°F)             | 39dB(A)  |
| Operational ambient temperature                | 0-40°C / 32°-104°F   |
| Operational humidity                           | 0-80% (non condens)  |
| Dissipation BTU                                | max 2900 BTU/h   |
| Dimensions (WxLxH)                             | 500 x 669.74 x 247mm / 19.69 x 26.36 x 9.72 inches   |
| Weight   | 26kg (57.3lbs)   |
| Shipping Dimensions                            | (LxWxH) 820 x 660 x 380mm / 32.28 x 25.98 x 14.96 inches   |
| Shipping Weight from Factory                   | 30kg (66.1lbs)   |
| Standard accessories                           | Power cord, wireless remote control, HDMI to DVI converter   |
| Certifications                                 | Compliant with FCC rules and regulations, part 15 Class A and CE EN55022 Class A, CE, TUV, RoHS, WEEE  |
| Warranty                                       | 3 years standard, 4th or 5th year optional   |
| *  | +/-10%   |

Gerada em: 20 Dec 2018

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte [www.barco.com](http://www.barco.com) para as últimas informações.