

# Lente EN26 de telezoom longo



Faixa de Foco: 5,0 - 25,0 m

- 3,90 - 6,24: 1 (1080p)
- 3,90 - 6,24: 1 (WUXGA)

**ESPECIFICAÇÕES TÉCNICAS****LENTE EN26 DE TELEZOOM LONGO**

---

<b>Working F/#</b>	F 2.6-3.4 Voice coil operated Iris F 2.6-7.0
<b>Zoom ratio</b>	1.6 Motorized zoom and focus
<b>Focal length</b>	82.55-132.0 mm
<b>Focus Range</b>	Standard: 5-25 m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	3.6 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ SXGA+ 4.3-6.89 :1</li><li>■ 1080p/Wuxga 3.9-6.24 :1</li></ul>

---

Image size tolerance +/-5%

Gerada em: 21 Jan 2018

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte [www.barco.com](http://www.barco.com) para as últimas informações.