

S3-4K

Processador Event Master compacto e expansível



- **Suporte para entrada e saída 4K nativa**
- **Expansão facilitada graças à intervinculagem do chassi**
- **Design compacto e modular**

Recursos poderosos, fácil operação

- Design modular baseado em placas
- A intervinculagem do chassi do S3-4K permite expansão de entradas, saídas e camadas
- Configuração fácil com a plataforma cruzada Event Master Toolset, oferecendo uma abordagem passo a passo para configuração do sistema
- Através das placas modulares iguais aos do E2, a manutenção do S3-4K pode ser realizada no campo e o equipamento está pronto para interfaces de sinais futuras
- Fontes de alimentação redundantes duplas para máxima tranquilidade
- Suporte para combinação de widescreen

ESPECIFICAÇÕES TÉCNICAS**S3-4K**

Model	NGS-3U
Live effects canvas	Up to 20 megapixels in PVW/PGM or 40 megapixels in PGM only mode
Video inputs	12 HD inputs via 3 input cards (Event Master series cards) <ul style="list-style-type: none">■ Up to 3x 4K inputs - each input card supports up to 4K@60p■ 4x SD/HD/3G SDI■ 4x HDMI 1.4a (297 MHz max)■ 4x DisplayPort 1.1 (300 MHz max)
Video outputs	12 HD outputs via 3 output cards (Event Master Series Cards) <ul style="list-style-type: none">■ Up to 3x 4K outputs - each output card supports up to 4K@60 p■ 4x SD/HD/3G SDI (6G reay)■ 4x HDMI 1.4a (297 MHz max)■ 2x HDMI 1.4a for Multiviewer (297 MHz max) or 4x HDMI 1.4a when used as standard output card
Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
Program output	Up to 12 outputs configurable as single screens or tiled/blended widescreens (preview and Multi-Viewer not available in all configurations). Configurable for up to 12x 2048X1200@60 or up to 3x 4096x2400@60 Independent edge blending/feathering control for all four sides.
Scaled Aux outputs	User-definable from 12x 2048x1200@60 to 3x 4K@60 All outputs can be defined as Aux destinations for a total of 12 Aux outputs Output color correction
Mixers	<ul style="list-style-type: none">■ Native resolution background mixer per output screen■ Independent layer transitions or full Preview/Program transition■ Flexible layer allocation - 4 mixable or 8 single scalable PIP/key layers assignable to any Program output screen
Still stores	Up to 100 HD or 25 UHD, depending on the import file size
Layer effects	<ul style="list-style-type: none">■ Borders (hard, soft, halo) and drop shadows■ Color effects■ Strobe, H&V flip■ Luma, chroma and Cut/Fill keys (not all modes support keying)■ PIP moves via Keyframes
Multiviewer	<ul style="list-style-type: none">■ Flexible user-definable layouts■ Monitor all Inputs and Outputs, including Preview and Aux■ Two outputs■ Dedicated hardware same as E2 Event Master Processor
Expandability	Easily expandable for larger display applications via proprietary links Link units to increase available Inputs and Outputs for larger tiled/blended widescreen applications Expansion via simple linking to 1xE2 or 4x EX chassis, or up to 7 more S3-4K chassis S3-4K ships with the ability to link 8 chassis for expansion
HDCP	HDCP compliance determined by installed cards.

ESPECIFICAÇÕES TÉCNICAS**S3-4K**

Control	<ul style="list-style-type: none">■ Event Master screen management software for PC or Mac■ Event Master Controllers■ WebUI■ Ethernet RJ-45, 1000/100/10 Mbps autosense
Serviceability	<ul style="list-style-type: none">■ Field-serviceable I/O and processing cards (not hot-swappable)■ Hot swappable dual-redundant power supplies
Noise Level	Max 51.3 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779
Dimensions	<ul style="list-style-type: none">■ Height: 13.26 cm / 5.22" - 3 RU rack mount■ Width: 43.2 cm / 17" without chassis handles, 48.3 cm / 19" with chassis handles attached■ Depth: 54 cm / 21.33" overall
Weight	24 kg / 53 lbs
Power	Input power: 100-240 VAC 50/60Hz 826 Watt Dual-redundant, hot-swappable power supplies
Environmental temperature	0-40° C / 32-104 F
Environmental humidity	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
Warranty	3 years parts and labor

Gerada em: 07 May 2021

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte www.barco.com para as últimas informações.