

# SLM R10 Performer

A Compact Projector for Rental & Staging Applications



**ТЕХНИЧЕСКИЕ ХАРАКТЕРИСТИКИ****SLM R10 PERFORMER**

<b>Light output</b>	10.000 ANSI Lumen
<b>Digital MicroMirror Device™</b>	3 high resolution SXGA DMD™'s
<b>Resolution</b>	1280 x 1024 (native) 1600 x 1200 (max)
<b>Brightness uniformity</b>	90 %
<b>Contrast</b>	Normal mode: 800 : 1 High mode: 1600 : 1 (Full White/Full Black)
<b>Lamp</b>	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp power: 2,2 kW
<b>Noise level (@ 20°C -68°F)</b>	< 56
<b>Noise level (@ 40°C -104°F)</b>	< 58
<b>Mains Voltage</b>	200-240 V
<b>Power consumption</b>	2750 W
<b>Ambient temperature</b>	35°C (95 F)
<b>Size</b>	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
<b>Weight (including rigging gear)</b>	57 kg (126 lbs)
<b>Lenses</b>	BARCO's "click-and-play™" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
<b>Lens Shift</b>	Motorized V shift: up to 100% Motorized H shift: up to 65%
<b>Sealed DLP™ core</b>	No
<b>Seamless Switching</b>	Standard
<b>ScenergiX</b>	Standard
<b>Network connection</b>	Optional
<b>Fixed Inputs</b>	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals  · 2 Multistandard DVI  · SDI input (Serial Digital Input)
<b>Optional Inputs</b>	One free digital input slot for optional input modules:  · SDI · HD -SDI
<b>Remote control</b>	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control  · Communication input (D9-connector) for peripherals  · 3 pin male XLR connector for wired remote (standard remote)  · 3 pin female XLR connector for bi-directional communication (rugged remote)

**Создано: 24 Feb 2021**

Технические характеристики могут изменяться без предварительного уведомления. Для получения самой последней информации посетите веб-сайт [www.barco.com](http://www.barco.com).