

Event projectors

3-chip DLP laser projectors

UDM Typical applications: concerts, corporate events, projection mapping

UDM-4K22
UDM-W22



Key specifications

- WUXGA and 4K UHD resolutions
- 22K lumens
- Barco Pulse electronics with SSP
- Flex² feature with minimal brightness loss
- Insights Dashboard for cloud-based fleet management

Description

Weighing less than 50 kilograms, the latest Barco projector is the lightest 22K laser projector on the market. But while the slim design minimizes installation time and reduces shipping and labor costs, it never compromises on brightness level, color reproduction or image quality. This versatile projector has an extensive list of peripherals at its disposal enabling the best results in the most diverse setups without complicating the installation process. In addition the rugged UDM is specifically designed to withstand the endurances of life on the road.

UDX Typical applications: concerts, large corporate events, shopping malls, architectural projection mapping

UDX-W22
UDX-4K22
UDX-W26
UDX-4K26
UDX-W32
UDX-4K32
UDX-U40
UDX-W40
UDX-4K40



Key specifications

- WUXGA and 4K UHD resolutions
- 26K, 32K and 40K lumens
- Barco Pulse electronics with SSP
- Flex² feature with minimal brightness loss

Description

As the brightest compact laser projector on the market, the UDX brings reliable and razor-sharp 4K images to every type of event and venue. Thanks to the laser phosphor light source and the Constant Light Output, you increase uptime while driving maintenance down. Its compact and rugged design enables you to reduce your shipping and labor costs. The Flex² feature allow you to regulate brightness and resolution, to fit your specific needs.

XDL Typical applications: 3D mapping, theme parks, CAD design centers

XDL-4K30
XDL-4K60
XDL-4K75



Key specifications

- 4K resolution (4096x2160)
- 30K, 60K and 75K lumens
- RGB laser
- Barco Pulse electronics

Description

75,000 lumens – from just one projector. With REC. 2020 colors that are just extraordinary. For bigger screens, more pixels, more impact. Plus incredible RGB laser performance, signal flexibility up to a comfortable 120 Hz, and no alignment. Offer visitors crisper, more realistic contrast for greater impact with images of breath-taking depth thanks to their native 4K resolution up to 120Hz. And when you need it, use brightness up to a massive 75L lumens – the brightest on the planet.

Single-chip DLP laser projectors

F80 Typical applications: small corporate events, breakout rooms at larger corporate events

F80-Q7
F80-4K7
F80-Q9
F80-4K9
F80-Q12
F80-4K12



Key specifications

- WQXGA and 4K UHD resolutions
- 7K, 9K and 12K lumens
- 24/7 operation
- Barco Pulse electronics with SSP
- Ultra-silent

Description

The stunning image quality and laser phosphor light source of Barco's F80 projectors enable you to provide exceptional experiences while saving both time and money. They're originally designed for fixed installations, such as museums, but thanks to their 3D capability, they're also perfectly fit for theme park dark rides and interactive experiences. The F80 delivers stunning images at up to 4K UHD resolution with highly saturated colors that allow for accurate color reproduction at all times. What's more it features the powerful Barco Pulse processing that allows for sharper images and less latency thanks to its Single Step Processing (SSP).

M00864-R02-0619-LC June 2019